

Retro Parabolic Louver for Lay-In Fixture

FEATURES & SPECIFICATIONS

INTENDED USE

This provides a bold look and superior lamp obscuration of the deep cell louver creates a dramatic appearance. The louver features extraordinary efficiency and light control with a low brightness accent in a grid ceiling. Standard finish is non-iridescent Semi-Specular Silver.

Aluminum is ideal for easy maintenance, cleaning, and durability. Fingerprints wipe off with a damp cloth.

Convert and standard recessed fluorescent fixture to a high tech, low brightness luminaire. It's as simple as 1, 2, 3. It's economical and immediately available in stock.




APPLICATIONS:

- Medical Facilities
- Department Stores
- Showrooms
- Commercial & Municipal Buildings
- Entries & Corridors
- Office Task Areas
- Banks
- Conference Rooms

Catalog No.	Nominal Size	Number of Cells	Cell Configuration
PL-131-23-6C	1' x 4'	6	1 row of 6
PL-131-12-8C	1' x 4'	8	1 row of 8
PL-131-12-16C	1' x 4'	16	2 rows of 8
PL-131-22-9C	2' x 2'	9	3 rows of 3
PL-131-22-16C	2' x 2'	16	4 rows of 4
PL-131-24-12C	2' x 4'	12	2 rows of 6
PL-131-24-18C	2' x 4'	18	3 rows of 6
PL-131-24-24C	2' x 4'	24	4 rows of 6
PL-131-24-32C	2' x 4'	32	4 rows of 8

Catalog Number:
Notes:



How To Order Kwik Change™
Determine the size of the ceiling grid system. The retrofit system is available in 1'x4', 2'x2' and 2'x4'.



STEP 1: Remove old doorframe with diffuser. Raise light fixture and shift to the side.




STEP 2: Place new Kwik Change™ System on existing ceiling grid. Lift and shift inner frame and swing down.




STEP 3: Reach through open panel and replace light fixture on top of Kwik Change™ Retrofit System. To close, swing up inner frame and lift and shift to secure in position.

CELL CONFIGURATION

2' x 4' Panel



2' x 2' Panel



1' x 4' Panel

